



Image coming soon

Part Number : 1301490045
Product Description : Safeway Flanged
Receptacle with Locking Blade, 4 Pole/5 Wire,
NEMA L21-20, 3ø 208V
Series Number : 130149
Status : Active
Product Category : Wiring Devices
Engineering Number : 2781MB

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices

Series	130149
Description	Safeway Flanged Receptacle with Locking Blade, 4 Pole/5 Wire, NEMA L21-20, 3Ø 208V
IP Rating	N/A
NEMA Configuration	NEMA L21-20
Product Family	Heavy-Duty Industrial Wiring Devices
Product Name	Safeway
Specialty	N/A
Type	Receptacle
UPC	78678802781

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	3Ø 208V

Physical

Cord Type	N/A
Flange	Yes
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	4-pole/5-wire
Receptacle Type	Single