


## SHROUDED IDC HEADER & STACKER

(2.00 mm) .0787" PITCH • STMM/ZSTMM SERIES



### STMM/ZSTMM

Mates:  
TCSD (except -SR)

#### SPECIFICATIONS

**Insulator Material:**  
Black Liquid Crystal Polymer  
**Terminal Material:**  
Phosphor Bronze  
**Plating:**  
Sn or Au over  
50 μ" (1.27 μm) Ni  
**Operating Temp Range:**  
-55 °C to +105 °C with Tin;  
-55 °C to +125 °C with Gold

#### PROCESSING

**Lead-Free Solderable:**  
Yes  
**SMT Lead Coplanarity:**  
(0.10 mm) .004" max

STMM	1	NO. PINS PER ROW	02	PLATING OPTION	D	TAIL OPTION	OTHER OPTION
		04, 05, 06, 07, 08, 10, 12, 13, 14, 15, 17, 20, 22, 25 (Standard sizes)		-F = Gold flash on post, Matte Tin on tail  -L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail  -T = Matte Tin		Leave blank for Through-hole  -RA = Right-angle  -SM = Surface Mount	-“XX” = Polarized Position  -LC = Locking Clip (-SM only) (Manual placement required)  -K = (7.50 mm) .295" DIA Film Pick & Place Pad (-SM only)  -TR = Tape & Reel (-SM only)  -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-SM only)

ZSTMM	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	BODY HEIGHT	OTHER OPTION
		04, 05, 06, 07, 08, 10, 12, 13, 14, 15, 17, 20, 22, 25 (Standard sizes)	Specify LEAD STYLE from chart	-F = Gold flash on post, Matte Tin on tail  -L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail  -T = Matte Tin		-“XXX” = Body Height	-“XX” = Polarized Position

LEAD STYLE	A (OAL)	MAX BODY HEIGHT
-75	(9.58) 0.377	(7.42) 0.292
-62	(10.08) 0.397	(7.92) 0.312
-65	(10.49) 0.413	(8.33) 0.328
-73	(12.09) 0.476	(9.93) 0.391
-63	(14.10) 0.555	(11.94) 0.470
-66	(15.09) 0.594	(12.93) 0.509
-69	(15.60) 0.614	(13.44) 0.529
-74	(17.09) 0.673	(14.94) 0.588
-70	(17.60) 0.693	(15.44) 0.608
-71	(21.08) 0.830	(18.92) 0.745
-72	(21.62) 0.851	(19.46) 0.766

#### ALSO AVAILABLE

MOQ Required

Other sizes  
Other platings

**Notes:**  
For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

This Series is non-standard, non-returnable.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[STMM-110-02-G-D](#) [STMM-125-02-G-D](#) [STMM-105-02-T-D-SM-K](#) [STMM-105-02-S-D](#) [STMM-105-02-G-D](#) [STMM-107-02-S-D](#) [STMM-105-02-L-D](#) [STMM-113-02-S-D](#) [STMM-110-01-T-D](#) [STMM-112-02-G-D](#) [STMM-107-02-G-D](#) [STMM-110-02-S-D](#) [STMM-105-01-T-D](#) [STMM-110-02-G-D-SM-K-TR](#) [STMM-107-02-S-D-SM](#) [STMM-105-02-G-D-RA](#) [STMM-125-02-S-D-SM](#) [STMM-110-02-L-D](#) [STMM-125-02-T-D](#) [STMM-113-02-L-D](#) [STMM-105-02-G-D-SM](#) [STMM-105-02-S-D-SM](#) [STMM-113-02-T-D](#) [STMM-120-02-T-D](#) [STMM-110-02-T-D](#) [STMM-108-02-L-D](#) [STMM-105-02-L-D-SM](#) [STMM-108-02-T-D](#) [STMM-115-02-L-D](#) [STMM-120-02-S-D](#) [STMM-120-02-G-D](#) [STMM-115-02-F-D](#) [STMM-115-02-T-D](#) [STMM-108-02-G-D-RA](#) [STMM-125-02-S-D](#) [STMM-125-02-S-D-RA](#) [STMM-108-02-S-D-SM](#) [STMM-115-02-G-D](#) [STMM-105-01-G-D](#) [STMM-107-02-S-D-RA](#) [STMM-110-02-F-D-SM](#) [STMM-125-02-L-D](#) [STMM-112-02-L-D](#) [STMM-105-02-F-D-SM-K-TR](#) [STMM-108-02-G-D](#) [STMM-108-02-F-D](#) [STMM-105-02-L-D-RA](#) [STMM-112-02-G-D-SM](#) [STMM-107-02-L-D-SM](#) [STMM-105-02-S-D-RA](#) [STMM-105-02-T-D](#) [STMM-110-02-L-D-SM](#) [STMM-105-02-F-D-SM](#) [STMM-120-02-L-D](#) [STMM-108-02-L-D-SM-LC](#) [STMM-107-02-L-D](#) [STMM-105-02-S-D-SM-K-TR](#) [STMM-105-02-G-D-SM-K-TR](#) [STMM-125-02-L-D-SM](#) [STMM-110-02-G-D-05](#) [STMM-107-02-T-D-SM](#) [STMM-110-02-G-D-SM-LC-K-TR](#) [STMM-112-01-T-D](#) [STMM-117-02-T-D-SM](#) [STMM-117-02-T-D](#) [STMM-116-02-T-D-SM](#) [STMM-116-01-L-D-SM](#) [STMM-105-02-G-D-SM-K](#) [STMM-104-02-L-D-SM](#) [STMM-105-02-T-D-SM](#) [STMM-107-02-G-D-SM](#) [STMM-112-02-T-D-SM](#) [STMM-120-02-T-D-SM-LC-TR](#) [STMM-106-02-T-D-SM-K-TR](#) [STMM-110-02-T-D-SM-K](#) [STMM-105-02-L-D-SM-K](#) [STMM-108-02-L-D-SM](#) [STMM-122-02-G-D](#) [STMM-110-02-F-D](#) [STMM-104-02-G-D-SM](#) [STMM-110-01-G-D](#) [STMM-105-02-F-D-SM-K](#) [STMM-108-02-S-D](#) [STMM-107-02-T-D-SM-K](#) [STMM-108-01-T-D](#) [STMM-112-02-T-D](#) [STMM-108-02-F-D-SM-K-TR](#) [STMM-105-02-F-D-RA](#) [STMM-107-02-T-D](#) [STMM-104-01-L-D-SM](#) [STMM-122-02-T-D](#) [STMM-105-02-G-D-SM-10-K-TR](#) [STMM-107-02-G-D-RA](#) [STMM-108-02-T-D-SM-K-TR](#) [STMM-108-02-G-D-SM-K-TR](#) [STMM-108-02-L-D-SM-TR](#) [STMM-105-02-S-D-SM-K](#) [STMM-105-02-G-D-P](#) [STMM-117-02-G-D](#) [STMM-108-02-G-D-SM](#)