



660-049 • 660-050
Composite MIL-DTL-38999 Series III
Protective Covers



Protective
Covers



660-049
MIL-DTL-38999/32
PLUG COVER



660-050
MIL-DTL-38999/33
RECEPTACLE COVER




TABLE I: CONNECTOR SHELL SIZE ORDER NUMBER

SHELL SIZE	A THREAD	B DIA MAX	C DIA MAX
09	.6250 -0.1P-0.3L-TS	.906 (23.0)	.906 (23.0)
11	.7500 -0.1P-0.3L-TS	1.024 (26.0)	1.102 (28.0)
13	.8750 -0.1P-0.3L-TS	1.220 (31.0)	1.220 (31.0)
15	1.0000 -0.1P-0.3L-TS	1.300 (33.0)	1.260 (32.0)
17	1.1875 -0.1P-0.3L-TS	1.457 (37.0)	1.457 (37.0)
19	1.2500 -0.1P-0.3L-TS	1.575 (40.0)	1.535 (39.0)
21	1.3750 -0.1P-0.3L-TS	1.732 (44.0)	1.654 (42.0)
23	1.5000 -0.1P-0.3L-TS	1.811 (46.0)	1.772 (45.0)
25	1.6250 -0.1P-0.3L-TS	1.969 (50.0)	1.929 (49.0)

Table II: Finish

Code	Finish Description
XM	1000 Hr. Corrosion-Resistant Electroless Nickel
XW	1000 Hr. Corrosion-Resistant Cadmium Olive Drab over Electroless Nickel
XB	No Plating - Black Color
XV	No Plating - Purple Color

Metric dimensions (mm) are in parentheses and are for reference only.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[660-050XW15U6-208](#) [660-049XW11U6-206](#) [660-049XW11U6-208](#) [660-049XW13N](#) [660-049XM09H5-05-59](#) [660-049XW21S6-109](#) [660-049XW25H6-24](#) [660-050XM11H5-106](#) [660-050XM13H5-107](#) [660-050XM17H6-05-186F](#) [660-050XW13D6-16](#) [660-050XW13H3-207](#) [660-049XM11N](#) [660-050XM25H5-113](#) [660-050XW21H5-111](#) [660-049XM09N](#) [660-049XM13N](#) [660-049XM15N](#) [660-050XM09N](#) [660-050XM11N](#) [660-050XM13N](#) [660-050XM21N](#) [660-049XM17N](#) [660-049XM19N](#) [660-049XM21N](#) [660-049XM23N](#) [660-049XM25N](#) [660-049XO11N](#) [660-049XO15N](#) [660-050XM15H6-05-186F](#) [660-050XM25H6.5-04](#) [660-050XW11U6-206](#) [660-049XO19N](#) [660-049XO21N](#) [660-050XM19N](#) [660-050XO15N](#) [660-050XO25N](#)