

COAXIAL CONNECTOR, UHF, X Ohm, Straight cable jack (female)
21_UHF-0-7-4/033_

Properties

- Mateable with 4 mm banana plugs
- Applicable in frequencies up to 200 MHz



Product configuration		
Interface type	Gender	Standard
UHF	jack	IEC 60169-12

Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data	
Interface frequency	0.2 GHz

Mechanical data	
Weight	0.0324 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-55 °C ... 165°C

Ordering Information Table	
Item number	Item description
22542775	21_UHF-0-7-4/033_-E

COAXIAL CONNECTOR, UHF, X Ohm, Straight cable jack (female)

21_UHF-0-7-4/033_

Suitable cables	
Cable group	U42 - 7 mm / 50 Ohm
	U29 - 7 mm / 50 Ohm
Suitable cables	GX_07272
	RG_213_/U
Additional cables	G_07272
	RADOX_RF_213
Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2825 / Date of publication: 25.11.2023 / uncontrolled copy