

Han B Protect Cover Die Cast for Base



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 006 5425
Specification	Han B Protect Cover Die Cast for Base
HARTING eCatalogue	https://b2b.harting.com/09300065425

Identification

Category	Accessories
Series of hoods/housings	Han® B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings Metal With fixing cord

Version

Size	6 B
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	44.1 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140044272
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors