

COAXIAL CONNECTOR, UHF, X Ohm, Straight panel receptacle, jack (female), flange mount

23_UHF-0-0-2/033_

Properties

- Mateable with 4 mm banana plugs
- Applicable in frequencies up to 200 MHz



Product configuration

Interface type	Gender	Standard
UHF	jack	IEC 60169-12

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data

Interface frequency	0.2 GHz
---------------------	---------

Mechanical data

Weight	0.0233 kg
Mating cycles	500
Flange type	square flange / 25.4 X 25.4
Tab style	solder end

Environmental data

Operation temperature	-55 °C ... 165°C
-----------------------	------------------

Ordering Information Table

Item number	Item description	Packaging type
22542788	23_UHF-0-0-2/033_-E	Single

COAXIAL CONNECTOR, UHF, X Ohm, Straight panel receptacle, jack (female), flange mount

23_UHF-0-0-2/033_

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2689 / Date of publication: 26.11.2023 / uncontrolled copy