

COAXIAL ADAPTER, N, 75 Ohm, L-style, plug / jack (male / female)

53_N-75-0-4/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials

**Product configuration**

Interface type	Gender	Standard
N	plug (male)	Not compatible to N 50 Ohms
N	jack (female)	Not compatible to N 50 Ohms

Interface and material data

N		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
N		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data

Impedance	75 Ω
Interface frequency	1.5 GHz

Mechanical data

Weight	0.0577 kg
Mating cycles	500

COAXIAL ADAPTER, N, 75 Ohm, L-style, plug / jack (male / female)
53_N-75-0-4/133_N

Environmental data	
Operation temperature	-65 °C ... 165 °C

Ordering Information Table		
Item number	Item description	Packaging type
22651799	53_N-75-0-4/133_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1882 / Date of publication: 27.05.2024 / uncontrolled copy