

1334212

<https://www.phoenixcontact.com/us/products/1334212>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Singlemode SFP transceiver for transmission up to 1 Gbps over 10 km at wavelengths of 1,310 nm in the extended temperature range

Your advantages

- Maximum flexibility, thanks to the non-proprietary multi-source agreement (MSA)
- Superior system availability, thanks to Plug and Play during operation
- Future-proof, thanks to RoHS 2 conformity
- Maximum data transmission quality
- Interference-free data transmission, even for EMC-sensitive applications
- Reliable data transmission in the extended temperature range

Commercial data

Item number	1334212
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNJAB
GTIN	4063151633424
Weight per piece (including packing)	30 g
Weight per piece (excluding packing)	30 g
Customs tariff number	85176200
Country of origin	TW

Technical data

Dimensions

Width	13.7 mm
Height	13 mm
Length	57.3 mm

Material specifications

Housing material	Metal
------------------	-------

Interfaces

Transmission speed	1 Gbps
Wavelength	1310 nm

Product properties

Product type	SFP module
Type	SFP Modul
Connection profile	LC-Duplex
Type of packaging	Box packaging

Data management status

Article revision	00
------------------	----

Electrical properties

Transmission speed	1 Gbps
--------------------	--------

Connection data

Connection method	To insert in SFP slot
-------------------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

Standards and regulations

Laser class	1
-------------	---

FOC-TRX-SFP-1G-LX-ET - Transceiver



1334212

<https://www.phoenixcontact.com/us/products/1334212>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1334212>



cULus Recognized

Approval ID: E140403-20100913

FOC-TRX-SFP-1G-LX-ET - Transceiver



1334212

<https://www.phoenixcontact.com/us/products/1334212>

Classifications

ECLASS

ECLASS-11.0	27440392
ECLASS-12.0	27440392
ECLASS-13.0	27440392

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FOC-TRX-SFP-1G-LX-ET - Transceiver

1334212

<https://www.phoenixcontact.com/us/products/1334212>



Accessories

FOC-CAGE:SFP/SFP+:1X1:PI - Transceiver

1334220

<https://www.phoenixcontact.com/us/products/1334220>



Cage for the insertion of SFP or SFP+ transceivers

FOC-CAGE:SFP/SFP+:1X2:PI - Transceiver

1334221

<https://www.phoenixcontact.com/us/products/1334221>



Cage for the insertion of SFP or SFP+ transceivers

FOC-TRX-SFP-1G-LX-ET - Transceiver

1334212

<https://www.phoenixcontact.com/us/products/1334212>



FOC-CAGE:SFP/SFP+:1X4:PI - Transceiver

1334222

<https://www.phoenixcontact.com/us/products/1334222>

Cage for the insertion of SFP or SFP+ transceivers




FOC-CON:SFP/SFP+:20AU:SMT - PCB connector

1334224

<https://www.phoenixcontact.com/us/products/1334224>

SMD PCB connector for SFP and SFP+ transceivers



FOC-TRX-SFP-1G-LX-ET - Transceiver

1334212

<https://www.phoenixcontact.com/us/products/1334212>



FOC-LC:PA-ST:PA-OS2:D01/1 - FO patch cable

1115596

<https://www.phoenixcontact.com/us/products/1115596>

Single-mode OS2 duplex jumper, LC-ST, UPC polishing, length 1 m



FOC-LC:PA-LC:PA-OS2:D01/1 - FO patch cable

1115636

<https://www.phoenixcontact.com/us/products/1115636>

Single-mode OS2 duplex jumper, LC-LC, UPC polishing, length 1 m



FOC-TRX-SFP-1G-LX-ET - Transceiver



1334212


<https://www.phoenixcontact.com/us/products/1334212>

FOC-LC:PA-SC:PA-OS2:D01/1 - FO patch cable

1115618

<https://www.phoenixcontact.com/us/products/1115618>

Single-mode OS2 duplex jumper, LC-SC, UPC polishing, length 1 m




FOC-LC:PA-SC:PA-OS2:D01/2 - FO patch cable

1115617

<https://www.phoenixcontact.com/us/products/1115617>

Single-mode OS2 duplex jumper, LC-SC, UPC polishing, length 2 m



FOC-TRX-SFP-1G-LX-ET - Transceiver

1334212

<https://www.phoenixcontact.com/us/products/1334212>



FOC-LC:PA-LC:PA-OS2:D01/2 - FO patch cable

1115629

<https://www.phoenixcontact.com/us/products/1115629>

Single-mode OS2 duplex jumper, LC-LC, UPC polishing, length 2 m



FOC-LC:PA-ST:PA-OS2:D01/2 - FO patch cable

1115595

<https://www.phoenixcontact.com/us/products/1115595>

Single-mode OS2 duplex jumper, LC-ST, UPC polishing, length 2 m



FOC-TRX-SFP-1G-LX-ET - Transceiver

1334212

<https://www.phoenixcontact.com/us/products/1334212>




FOC-LC:PA-LC:PA-OS2:D01/5 - FO patch cable

1115626

<https://www.phoenixcontact.com/us/products/1115626>

Single-mode OS2 duplex jumper, LC-LC, UPC polishing, length 5 m




FOC-LC:PA-SC:PA-OS2:D01/5 - FO patch cable

1115615

<https://www.phoenixcontact.com/us/products/1115615>

Single-mode OS2 duplex jumper, LC-SC, UPC polishing, length 5 m



FOC-TRX-SFP-1G-LX-ET - Transceiver

1334212

<https://www.phoenixcontact.com/us/products/1334212>



FOC-LC:PA-ST:PA-OS2:D01/5 - FO patch cable

1115592

<https://www.phoenixcontact.com/us/products/1115592>

Single-mode OS2 duplex jumper, LC-ST, UPC polishing, length 5 m



Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com