



Pushing Performance
Since 1945

Han Q 8/0 ABDECKKAPPE



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 008 5407
Specification	Han Q 8/0 ABDECKKAPPE
HARTING eCatalogue	https://b2b.harting.com/09120085407

Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings Thermoplastic

Version

Size	Han-Compact®
Locking type	Single locking lever
Details	for mounted male insert

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	10
Net weight	7 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140017962
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors