

Han 16A/25EMV-AK f. Easy-Lock



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 016 5425
Specification	Han 16A/25EMV-AK f. Easy-Lock
HARTING eCatalogue	https://b2b.harting.com/09200165425

Identification

Category	Accessories
Series of hoods/housings	Han A®
Type of accessory	Protection cover
	for bulkhead mounted housings
	for surface mounted housings
Description of the accessory	for cable to cable housing Metal With fixing cord

Version

Size	16 A
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
	4
Type rating acc. to UL 50 / UL 50E	4X
	12

Material properties

Surface (hood/housing)	Powder-coated
Material (seal)	NBR
RoHS	compliant
ELV status	compliant

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	41 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140039988
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors