

Han P male crimp contact 0,75 mm² (Ag)



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 000 6104
Specification	Han P male crimp contact 0,75 mm ² (Ag)
HARTING eCatalogue	https://b2b.harting.com/09350006104

Identification

Category	Contacts
Series	Han [®] PushPull (V14)
Type of contact	Crimp contact
Description of the contact	Straight

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.75 mm ²
Conductor cross-section	AWG 18
Stripping length	6 mm
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 61076-3-118
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	100
Net weight	0.96 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140229174
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors