



Pushing Performance
Since 1945

Han-Eco Mod.10-C-f. HCC-cord loop



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 010 5402
Specification	Han-Eco Mod.10-C-f. HCC-cord loop
HARTING eCatalogue	https://b2b.harting.com/19410105402

Identification

Category	Accessories
Series of hoods/housings	Han-Eco® Modular
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings
	for surface mounted housings
	for cable to cable housing
	With fixing cord (loop)

Version

Size	10 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polyamide (PA)
	Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61984 EN 45545-2 Fire protection on railway vehicles
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	46.6 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140130920
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors