

## Han 48HPR cover angled housing 5xM32



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 048 9812
Specification	Han 48HPR cover angled housing 5xM32
HARTING eCatalogue	<a href="https://b2b.harting.com/19400489812">https://b2b.harting.com/19400489812</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Mounting cover
Description of hood/housing	Distance bolt M6

### Version

Size	48 B
Cable entry	5x M32
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	4 distance pieces 4x M6 screw 4 washers

### Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653

### Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
-------------------------	---

## Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	623.8 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140173538
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors