

Han 10A/15EMV-AK



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 010 5425
Specification	Han 10A/15EMV-AK
HARTING eCatalogue	https://b2b.harting.com/09200105425

Identification

Category	Accessories
Series of hoods/housings	Han A®
Type of accessory	Protection cover
	for bulkhead mounted housings
	for surface mounted housings
Description of the accessory	for cable to cable housing
	Metal
	With fixing cord

Version

Size	10 A
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
	4
Type rating acc. to UL 50 / UL 50E	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(b) / 6(b)-II: Lead as an alloying element in aluminium containing up to 0,4 % lead by weight / Lead as an alloying element in aluminium for machining purposes with a lead content up to 0,4 % by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	56 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140039568
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors