

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731120488

Status:

Active

Overview:

FCT D-Sub Connectors

Description:

FCT Stamped Contact, Male, Crimp, 0.80µm Gold Plating, 24-28 AWG

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	D-Sub Products
Series	173112
Contact Type	Stamped Crimp
Overview	FCT D-Sub Connectors
Product Category	Contacts
Product Name	FCT Products
Type	Standard Density
UPC	191128237888
Physical	
Durability (mating cycles max)	500
Gender	Male
Material - Contact	Copper Alloy
Net Weight	0.200/g
Orientation	Straight
Packaging Type	Reel
Plating - Contact	Gold over Nickel
Plating min - Mating	0.800µm
Temperature Range - Operating	-55° to +125°C
Termination Style	Crimp
Wire Size AWG	24, 26, 28
Electrical	
Current - Maximum per Contact	5.0A
Material Info	
Engineering Number	P7LSR26-K176



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

173112 Series

Use With

FCT Standard-Density Connectors

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION