

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [1301550137](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Safeway Single Flanged Inlet with California Style Locking Blade, 3 Pole/4 Wire, Non-NEMA, 125/250V

**Documents:**  
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

|                               |                                                      |
|-------------------------------|------------------------------------------------------|
| <b>General</b>                |                                                      |
| Product Family                | Wiring Devices                                       |
| Series                        | <a href="#">130155</a>                               |
| IP Rating                     | N/A                                                  |
| NEMA Configuration            | Non-NEMA Locking CA                                  |
| Overview                      | <a href="#">Heavy-Duty Industrial Wiring Devices</a> |
| Product Name                  | Safeway                                              |
| Receptacle Type               | N/A                                                  |
| Specialty                     | N/A                                                  |
| Type                          | Inlet                                                |
| UPC                           | 78678850925                                          |
| <b>Physical</b>               |                                                      |
| Flange                        | Yes                                                  |
| Flip Lid                      | No                                                   |
| Gender                        | Male                                                 |
| Length                        | N/A                                                  |
| Locking Blade                 | Yes                                                  |
| Poles                         | 3-pole/4-wire                                        |
| <b>Electrical</b>             |                                                      |
| Cord Type                     | N/A                                                  |
| Current - Maximum per Contact | 50.0A                                                |
| GFCI                          | No                                                   |
| Lighted Connector             | No                                                   |
| Voltage - Maximum             | 125V / 250V                                          |
| <b>Material Info</b>          |                                                      |
| Engineering Number            | CS6375                                               |



Series image - Reference only

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                          |                   |
| <b>EU RoHS</b><br><b>Not Relevant</b>                         | <b>China RoHS</b> |
| <b>REACH SVHC</b><br>Not Relevant                             |                   |
| <b>Halogen-Free</b><br><b>Status</b><br><b>Not Relevant</b>   |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Relevant      |
| ELV                                                           | Not Relevant      |
| RoHS Phthalates                                               | Not Relevant      |

**Search Parts in this Series**  
[130155](#) Series

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301550137](#)