



Part Number : [936010479](#)
Product Description : GWconnect Turned Crimp Contact for 5A D-Sub Inserts and Modules, Male, Gold (Au) Plated Copper Alloy, 0.08-0.20mm² (28-24 AWG), 100 per Bag
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Contacts
Engineering Number : 7700.3440.1




Documents & Resources

Drawings
[936010479_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Heavy-Duty Contacts
Series	93601
Description	GWconnect Turned Crimp Contact for 5A D-Sub Inserts and Modules, Male, Gold (Au) Plated Copper Alloy, 0.08-0.20mm ² (28-24 AWG), 100 per Bag
Contact Type	Turned Crimp
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
UPC	887191892870

Electrical

Current - Maximum per Contact	5.0A
-------------------------------	------

Physical

Gender	Male
Material - Contact	Copper Alloy
Material - Plating	Gold
Net Weight	0.190/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	5.00mm
Wire Size (AWG)	24, 26, 28
Wire Size mm ²	0.08-0.20

Mates With / Use With

Mates with Part(s)

Description	Part Number
-------------	-------------

GWconnect Heavy-Duty Connectors and Accessories	<u>93601</u>
--	--------------

Use with Part(s)

Description	Part Number
Use With	D-Sub Connectors
