



Sav-Con® Connector Savers

MIL-DTL-38999 Series III


941-005 and 942-005 Threaded Coupling



941-005 ENVIRONMENTAL AND 942-005 HIGH RELIABILITY THREADED COUPLING

941-005 and 942-005 are unavailable for new design. Please refer to 233-213 for new applications.

How To Order								
Sample Part Number	94	1	-005	NF	B	98	P	A
Series	94							
Class	1 = Environmental 2 = High Reliability							
Basic Number	005							
Finish	See Table I							
Shell Size	A, B, C, D, E, F, G, H, J See Table II or Dimensions Table							
Insert Arrangement	See Table II							
Contact Type	P = Pins, Plug Side (Socket, Receptacle Side) S = Sockets, Plug Side (Pin, Receptacle Side)							
Alternate Key Position	A, B, C, D, E, N = Normal; See Table III							



Dimensions			
Shell Size Ref	Shell Size	A Thread Class 2	B Max
A	9	.6250 - 0.1P - 0.3L - TS-2	.858 (21.82)
B	11	.7500 - 0.1P - 0.3L - TS-2	.984 (24.61)
C	13	.8750 - 0.1P - 0.3L - TS-2	1.157 (28.98)
D	15	1.0000 - 0.1P - 0.3L - TS-2	1.280 (32.16)
E	17	1.1875 - 0.1P - 0.3L - TS-2	1.406 (35.33)
F	19	1.2500 - 0.1P - 0.3L - TS-2	1.516 (38.10)
G	21	1.3750 - 0.1P - 0.3L - TS-2	1.642 (41.28)
H	23	1.5000 - 0.1P - 0.3L - TS-2	1.768 (44.45)
J	25	1.6250 - 0.1P - 0.3L - TS-2	1.890 (47.63)



Sav-Con® connector savers

MIL-DTL-38999 Series III


Reference Information



Table I: Material and Finish		
Plating Code	Material	Finish
M	Aluminum	Electroless Nickel
B		Cad Plate, Olive Drab
NF		Cadmium Plate Olive Drab over Electroless Nickel
NC		Zinc-Cobalt
ZN		Olive Drab Zinc-Nickel
MT		Ni-PTFE 1000 Hour Grey™ (Nickel Fluorocarbon Polymer)
ZR		Zinc Nickel, Black
ME		Electroless Nickel (RoHS)
ZL	Stainless Steel	Electro-Deposited Nickel

Table III: Manin and Alternate Keyway Positions

Shell Size Code Ref	Shell Size	Alt. Keyway Code	AR°	BR°	CR°	DR°
A	9	N	105	140	215	265
		A	102	132	248	320
		B	80	118	230	312
		C	35	140	205	275
		D	64	155	234	304
		E	91	131	197	240
B	11	N	95	141	208	236
		A	113	156	182	292
	13	B	90	145	195	252
		C	53	156	220	255
	15	D	119	146	176	298
		E	51	141	184	242
E	17	N	80	142	196	293
		A	135	170	200	310
	19	B	49	169	200	244
		C	66	140	200	257
		D	62	145	180	280
		E	79	153	197	272
G	21	N	80	142	196	293
		A	135	170	200	310
	23	B	49	169	200	244
		C	66	140	200	257
		D	62	145	180	280
		E	79	153	197	272



FACE VIEW
RECEPTACLE INSERT



Sav-Con® connector savers

MIL-DTL-38999 Series III

Reference Information



Table II: Shell Size - Insert Arrangement						
Shell Size Code	Shell Size Ref.	Insert Arr. Dash No.	Contact Size			
			22	20	16	12
A	9	9-3		3		
		9-35	6			
		9-44	4			
		9-98		3		
B	11	11-2			2	
		11-4		4		
		11-5		5		
		11-6		6		
		11-35	13			
		11-98		6		
		11-99		7		
C	13	13-4			4	
		13-8		8		
		13-35	22			
		13-98		10		
D	15	15-5			5	
		15-15		14	1	
		15-18		18		
		15-19		19		
		15-35	37			
		15-97		8	4	
E	17	17-6				6
		17-8			8	
		17-26		26		
		17-35	55			
		17-99		21	2	
F	19	19-11			11	
		19-28		26	2	
		19-30		29	1	
		19-32		32		
		19-35	66			
		19-45	67			

Table II: Shell Size - Insert Arrangement						
Shell Size Code	Shell Size Ref.	Insert Arr. Dash No.	Contact Size			
			22	20	16	12
G	21	21-35	79			
		21-11				11
		21-16			16	
		21-24		24		
		21-25		25		
		21-27		27		
		21-39		37	2	
		21-41		41		
H	23	23-35	100			
		23-2	85			
		23-21			21	
		23-32		32		
		23-34		34		
		23-36		36		
		23-53		53		
		23-55		55		
		23-97			16	
		23-99			11	
J	25	25-2	100			
		25-4		48	8	
		25-19				19
		25-24			12	12
		25-29			29	
		25-35	128			
		25-43		23	20	
		25-61		61		

Table IV: Capacitor Array Code Capacitance Range for Filtered Connectors		
Class	Pi - Circuit (pF)	C - Circuit (pF)
X*	160,000 - 240,000	80,000 - 120,000
Y*	80,000 - 120,000	40,000 - 60,000
Z*	60,000 - 90,000	30,000 - 45,000
A	38,000 - 56,000	19,000 - 28,000
B	32,000 - 45,000	16,000 - 22,500
C	18,000 - 33,000	9,000 - 16,500
D	8,000 - 12,000	4,000 - 6,000
E	3,300 - 5,000	1,650 - 2,500
F	800 - 1,300	400 - 650
G	400 - 600	200 - 300
J	70-120	35-60

* Filter Classes X, Y and Z are 250 VDC.
All others are 500 VDC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Glenair:](#)

[941-005MB35SA-1R](#) [941-005MB35SB-1R](#) [941-005MB35SN-1R](#) [941-005MC35PN-1R](#) [941-005MC35SA-1R](#) [941-005MC35SB-1R](#) [941-005MC35SC-1R](#) [941-005MC35SN-1R](#) [941-005MC8SA-1R](#) [941-005MC8SN-1R](#) [941-005MD19SA-1R](#) [941-005MD19SB-1R](#) [941-005MD19SC-1R](#) [941-005MD19SN-1R](#) [941-005MD35PB-1R](#) [941-005MD35SA-1R](#) [941-005MD35SB-1R](#) [941-005MD35SN-1R](#) [941-005ME26SN-1R](#) [941-005ME35SB-1R](#) [941-005ME8SA-1R](#) [941-005ME8SN-1R](#) [941-005MF35SN-1R](#) [941-005MG16SA-1R](#) [941-005MG16SN-1R](#) [941-005MG35PC-1R](#) [941-005MG35PN-1R](#) [941-005MG35SN-1R](#) [941-005MG41SB-1R](#) [941-005MG41SN-1R](#) [941-005MH21PA-1R](#) [941-005MH21PN-1R](#) [941-005MH55SN-1R](#) [941-005MJ43PA-1R](#) [941-005MJ43PN-1R](#) [941-005MJ43SA-1R](#) [941-005MJ43SN-1R](#) [941-005MB35SC-1R](#) [941-005MB35SD-1R](#) [941-005MB98SD-1R](#) [941-005MB98SE-1R](#) [941-005MH55SA-1R](#) [941-005MD35SC-1R](#) [941-005MC35PN](#) [941-005MD35PN](#) [941-005MD35SN](#) [941-005MG35PN](#) [941-005MG35SN](#) [941-005NFD35PN](#) [941-005NFE35PN](#) [941-005NFE35SN](#) [941-005NFB35SN](#) [941-005NFB35SN](#) [942-005MA35SN](#) [942-005MB35PN](#) [942-005MB35SN](#) [942-005MB98SN](#) [942-005ME35SA-131](#) [942-005MF35S-186](#) [942-005MJ35SN](#) [941-005MF35PB](#) [941-005MH35PB-429A](#) [941-005NFF11PN](#) [941-005NFF11SN](#) [941-005MJ29PN](#) [941-005MJ43PA](#) [941-005NFB35PN](#) [941-005MJ35PN](#) [941-005NF35SN](#) [941-005NFF35SN](#) [941-005NFB35SN-98](#) [941-005NFF35SN-98](#) [941-005MH55PN](#) [941-005M35PN](#) [942-005MD18SN](#) [942-005MJ35PN](#) [942-005ME6PN](#) [942-005MD18PN](#) [942-005MF35PN](#) [941-005NFD15SN](#) [941-005ME26SNPB](#) [941-005MH35SN](#) [942-005MD35PN](#) [942-005MA35PN](#) [942-005MF32PN](#) [941-005MC4SN](#) [941-005ME35SN](#) [941-005MD35PC](#) [942-005MG41P](#) [942-005MJ35SB](#) [942-005MA98SN](#) [942-005MB35P](#) [942-005MC35P](#) [942-005MC35PC](#) [942-005MC35SA](#) [942-005MF35SN](#) [942-005MJ19PN](#) [942-005MJ35PC](#) [942-005MJ61SN](#) [941-005MF35SB](#)