

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ferrules, taped, 0.25 mm², sleeve length: 8 mm, color: yellow (CF 3000-TOOLKIT 0,25 is required)



Your advantages

- The taped ferrules were developed specifically for the CF 3000-2,5 automatic crimping device
- Available in the main color ranges up to 2.5 mm²
- Can be used to wire all terminal blocks, especially those of the CLIPLINE complete system

Commercial data

Item number	3240251
Packing unit	1,000 pc
Minimum order quantity	1,000 pc
Sales key	BH34
Product key	BH3414
Catalog page	Page 515 (C-3-2019)
GTIN	4046356461412
Weight per piece (including packing)	0.104 g
Weight per piece (excluding packing)	0.099 g
Customs tariff number	85369010
Country of origin	DE

AI 0,25-8 YE-B - Ferrule

3240251

<https://www.phoenixcontact.com/us/products/3240251>



Technical data

Product properties

Product type	Cable end sleeve
Data management status	
Article revision	03

Connection data

Conductor connection	
Conductor cross section flexible max.	0.25 mm ²
Conductor cross section AWG max.	24
Stripping length	10 mm

Dimensions

Dimensional drawing	
Sleeve length	8 mm
Maximum stripping length	10 mm
Ferrule diameter	0.8 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.25 mm
Inner dimensions of the insulating collar	2.2 mm

Material specifications

Color	yellow (RAL 1018)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	tin-plated (galvanic)
Surface characteristics	Tin-plated
Components	free from silicone and halogen

Mechanical properties

Technical data	
Sleeve length	8 mm

Environmental and real-life conditions

Ambient conditions	
Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)
Short-term temperature	120 °C

Standards and regulations

Design according to standard

UL 486F-E

AI 0,25-8 YE-B - Ferrule


3240251

<https://www.phoenixcontact.com/us/products/3240251>



Drawings

Dimensional drawing



Length (b), sleeve length (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

AI 0,25-8 YE-B - Ferrule

3240251

<https://www.phoenixcontact.com/us/products/3240251>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240251>



cULus Listed

Approval ID: E488001

AI 0,25-8 YE-B - Ferrule

3240251

<https://www.phoenixcontact.com/us/products/3240251>



Classifications

ECLASS

ECLASS-11.0	27400201
ECLASS-13.0	27400201
ECLASS-12.0	27400201

ETIM

ETIM 9.0	EC000005
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com