



#### General ordering data

Order No.	1811540000
Part designation	LMZFL 5/5/135 3.5SW
Version	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 5, 135°, Box
EAN	4032248290642
Qty.	100 pc(s).

#### System parameters

Product family	System LM
Conductor connection system	Tension clamp connection
Fitted to PCB	Soldered connection
Outgoing direction of conductor	135°
Pitch	5 mm
Pitch in inch	0.197 inch
No. of poles	5
Max. adjacent poles per row	48
No. of rows	1
Solder pin length	3.5 mm
Dia. of fitting hole	1.3 mm
No. of solder pins per pole	2
Screwdriver blade	0.4 x 2.5
Stripping length	6 mm

**System parameters**

L1 in mm	20 mm
L1 in inch	0.787 inch
Electric shock protection to DIN VDE 0470	IP 20
Electric shock protection to DIN VDE 0470	Safe from finger touch

**Material data**

Insulating material	Wemid (PA)
Colour	black
colour chart	Similar to RAL 9011
Insulating material group	I
Flammability class UL 94	V-0
CTI	>= 600
Contact base material	E-Cu
Contact surface	tinned
Storage temperature, min.	-55 °C
Storage temperature, max.	120 °C

**Connectable conductors**

Clamping range, min.	0.13 mm <sup>2</sup>
Clamping range, max.	2.5 mm <sup>2</sup>
AWG, min.	26
AWG, max.	14
Solid, min. H05(07) V-U	0.13 mm <sup>2</sup>
Solid, max. H05(07) V-U	2.5 mm <sup>2</sup>
Flexible, min. H05(07) V-K	0.13 mm <sup>2</sup>
Flexible, max. H05(07) V-K	2.5 mm <sup>2</sup>
With wire end ferrule, acc. to DIN 46 228/1, min.	0.25 mm <sup>2</sup>
With wire end ferrule, acc. to DIN 46 228/1, max.	1.5 mm <sup>2</sup>
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.25 mm <sup>2</sup>
w. plastic collar ferrule, DIN 46228 pt 4, max.	1.5 mm <sup>2</sup>

**DIN IEC rating data**

Rated current, min. No. pins (Tu=20°C)	24 A
Rated current, max. No. pins (Tu=20°C)	24 A
Rated current, min. No. pins (Tu=40°C)	24 A
Rated current, max. No. pins (Tu=40°C)	24 A
Rated voltage for overvoltage class/pollution severity II/2	630 V
Rated voltage for overvoltage class/pollution severity III/2	320 V
Rated voltage for overvoltage class/pollution severity III/3	250 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	4 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	4 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	4 kV

**CSA rating data**

Rated voltage (Use group D)	300 V
-----------------------------	-------

**CSA rating data**

Rated current (Use group D)	10 A
AWG conductor (field wiring), min.	26
AWG conductor (field wiring), max.	14

**UL 1059 rating data**

Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A
AWG conductor, min.	26
AWG conductor, max.	14

**Approvals**

Approvals institutes

**Downloads**

CAD Library (P-CAD Format - Standard) LMZFL.LIB

**Classifications**

ETIM 2.0	NK
ETIM 3.0	EC001284
eClass 4.1	NK
eClass 5.0	NK
eClass 5.1	NK

**Similar products**

Order No.	Part designation	Version
1914560000	LMZFL 5/2/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 2, 135°, Box
1811510000	LMZFL 5/2/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 2, 135°, Box
1811620000	LMZFL 5/2/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 2, 135°, Box

1811730000	LMZFL 5/2/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 2, 135°, Box
1914580000	LMZFL 5/3/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 3, 135°, Box
1811520000	LMZFL 5/3/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 3, 135°, Box
1811630000	LMZFL 5/3/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 3, 135°, Box
1811740000	LMZFL 5/3/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 3, 135°, Box
1914590000	LMZFL 5/4/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 4, 135°, Box
1811530000	LMZFL 5/4/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 4, 135°, Box
1811640000	LMZFL 5/4/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 4, 135°, Box
1811750000	LMZFL 5/4/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 4, 135°, Box
1914600000	LMZFL 5/5/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 5, 135°, Box
1811650000	LMZFL 5/5/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 5, 135°, Box
1811760000	LMZFL 5/5/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 5, 135°, Box
1914640000	LMZFL 5/6/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 6, 135°, Box
1811550000	LMZFL 5/6/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 6, 135°, Box
1811660000	LMZFL 5/6/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 6, 135°, Box
1811770000	LMZFL 5/6/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 6, 135°, Box
1914720000	LMZFL 5/7/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 7, 135°, Box

1811560000	LMZFL 5/7/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 7, 135°, Box
1811670000	LMZFL 5/7/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 7, 135°, Box
1811780000	LMZFL 5/7/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 7, 135°, Box
1914790000	LMZFL 5/8/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 8, 135°, Box
1811570000	LMZFL 5/8/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 8, 135°, Box
1811680000	LMZFL 5/8/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 8, 135°, Box
1811790000	LMZFL 5/8/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 8, 135°, Box
1914830000	LMZFL 5/9/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 9, 135°, Box
1811580000	LMZFL 5/9/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 9, 135°, Box
1811690000	LMZFL 5/9/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 9, 135°, Box
1811800000	LMZFL 5/9/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 9, 135°, Box
1914860000	LMZFL 5/10/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 10, 135°, Box
1811590000	LMZFL 5/10/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 10, 135°, Box
1811700000	LMZFL 5/10/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 10, 135°, Box
1811810000	LMZFL 5/10/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 10, 135°, Box
1914990000	LMZFL 5/11/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 11, 135°, Box
1811600000	LMZFL 5/11/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 11, 135°, Box

1811710000	LMZFL 5/11/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 11, 135°, Box
1811820000	LMZFL 5/11/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 11, 135°, Box
1915030000	LMZFL 5/12/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 12, 135°, Box
1811610000	LMZFL 5/12/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 12, 135°, Box
1811720000	LMZFL 5/12/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 12, 135°, Box
1811830000	LMZFL 5/12/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 12, 135°, Box
1958320000	LMZFL 5/13/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 13, 135°, Box
1957720000	LMZFL 5/13/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 13, 135°, Box
1958070000	LMZFL 5/13/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 13, 135°, Box
1957920000	LMZFL 5/13/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 13, 135°, Box
1958330000	LMZFL 5/14/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 14, 135°, Box
1957730000	LMZFL 5/14/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 14, 135°, Box
1958080000	LMZFL 5/14/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 14, 135°, Box
1957930000	LMZFL 5/14/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 14, 135°, Box
1958350000	LMZFL 5/15/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 15, 135°, Box
1957740000	LMZFL 5/15/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 15, 135°, Box
1958100000	LMZFL 5/15/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 15, 135°, Box

1957940000	LMZFL 5/15/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 15, 135°, Box
1958370000	LMZFL 5/16/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 16, 135°, Box
1957750000	LMZFL 5/16/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 16, 135°, Box
1958110000	LMZFL 5/16/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 16, 135°, Box
1957950000	LMZFL 5/16/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 16, 135°, Box
1958390000	LMZFL 5/17/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 17, 135°, Box
1957760000	LMZFL 5/17/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 17, 135°, Box
1958140000	LMZFL 5/17/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 17, 135°, Box
1957970000	LMZFL 5/17/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 17, 135°, Box
1958410000	LMZFL 5/18/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 18, 135°, Box
1957770000	LMZFL 5/18/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 18, 135°, Box
1958150000	LMZFL 5/18/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 18, 135°, Box
1957980000	LMZFL 5/18/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 18, 135°, Box
1958440000	LMZFL 5/19/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 19, 135°, Box
1957790000	LMZFL 5/19/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 19, 135°, Box
1958170000	LMZFL 5/19/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 19, 135°, Box
1957990000	LMZFL 5/19/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 19, 135°, Box

1958450000	LMZFL 5/20/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 20, 135°, Box
1957810000	LMZFL 5/20/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 20, 135°, Box
1958180000	LMZFL 5/20/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 20, 135°, Box
1958000000	LMZFL 5/20/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 20, 135°, Box
1958470000	LMZFL 5/21/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 21, 135°, Box
1957840000	LMZFL 5/21/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 21, 135°, Box
1958200000	LMZFL 5/21/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 21, 135°, Box
1958010000	LMZFL 5/21/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 21, 135°, Box
1958490000	LMZFL 5/22/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 22, 135°, Box
1957860000	LMZFL 5/22/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 22, 135°, Box
1958210000	LMZFL 5/22/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 22, 135°, Box
1958020000	LMZFL 5/22/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 22, 135°, Box
1958500000	LMZFL 5/23/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 23, 135°, Box
1957870000	LMZFL 5/23/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 23, 135°, Box
1958220000	LMZFL 5/23/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 23, 135°, Box
1958030000	LMZFL 5/23/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 23, 135°, Box
1958510000	LMZFL 5/24/135 3.5OR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 24, 135°, Box

1957890000	LMZFL 5/24/135 3.5SW	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 24, 135°, Box
1958240000	LMZFL 5/24/135 3.5GR	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 24, 135°, Box
1958050000	LMZFL 5/24/135 3.5GN	PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm <sup>2</sup> , Pitch: 5.00 mm, No. of poles: 24, 135°, Box