



Part Number : [1301460121](#)
Product Description : Watertite Extreme
Female Receptacle with Single Flip Coverplate,
3 Pole/3 Wire, Non-NEMA 15A/125V,
10A/250V
Series Number : 130146
Status : Active
Product Category : Wiring Devices
Engineering Number : 60W07



Documents & Resources

Drawings
[1301460121_sd.pdf](#)

3D Models and Design Files
[1301460121_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Female Receptacle with Single Flip Coverplate, 3 Pole/3 Wire, Non-NEMA 15A/125V, 10A/250V
IP Rating	IP67
NEMA Configuration	Non-NEMA
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871480

Agency

UL	E68122
----	--------

Electrical

Current - Maximum per Contact	10.0A, 15.0A
GFCI	No
Voltage - Maximum	125V / 250V

Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female

Length	N/A
Lighted Connector	No
Locking Blade	No
Net Weight	9.240/g
Poles	3-pole/3-wire
Receptacle Type	Single