



Pushing Performance
Since 1945

Uni-Dicht-Verschraubung Pg13,5 6,5-9,5mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5083
Specification	Uni-Dicht-Verschraubung Pg13,5 6,5-9,5mm
HARTING eCatalogue	https://b2b.harting.com/09000005083

Identification

Category	Accessories
Type of accessory	Cable gland

Technical characteristics

Tightening torque	≤10 Nm (depending on the cable and the seal insert used)
Wrench size	22
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP68
Size	Pg 13.5
Clamping range	6.5 ... 9.5 mm

Material properties

Material (cable glands)	Metal
Colour (accessories)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Lead
	Nickel
	Naphthalene

Commercial data

Packaging size	10
Net weight	32.4 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140001640
ETIM	EC000441
eCl@ss	27140801 Screwed cable gland (electrical)