

PLUG		RECEPTACLE	
SERIES MM .050" Rugged Metal PC Board Mount, SMT Connector MN .050" Rugged Plastic PC Board Mount, SMT Connector (MM & MN mate with MK, ML, MM, MN receptacles)		SERIES MM .050" Rugged Metal I/O Connector MN .050" Rugged Plastic I/O Connector (MM & MN mate with MK, ML, MM, MN plugs)	
BODY 2 2-Row (Sizes 9 thru 51***) BODY STYLE: 1 Plug, straight, with ears BODY MATERIAL: 1 Polyphenylene Sulfide (MN only) 2 Polyphenylene Sulfide with electroless nickel shell 3 Polyphenylene Sulfide with electrodeposited cadmium shell ☒ 4 Polyphenylene Sulfide with hard anodized black shell 5 Polyphenylene Sulfide with stainless steel shell A Pure Electro-Deposited Aluminum K Zinc Nickel Plating T Nickel Polymer Plating		BODY 2 2-Row (Sizes 9 thru 51***) BODY STYLE: 2 Receptacle, straight, with ears BODY MATERIAL: 1 Polyphenylene Sulfide (MN only) 2 Polyphenylene Sulfide with electroless nickel shell 3 Polyphenylene Sulfide with electrodeposited cadmium shell ☒ 4 Polyphenylene Sulfide with hard anodized black shell 5 Polyphenylene Sulfide with stainless steel shell A Pure Electro-Deposited Aluminum K Zinc Nickel Plating T Nickel Polymer Plating	
SIZE XXX 009, 015, 021, 025, 031, 037, 051***		SIZE XXX 009, 015, 021, 025, 031, 037, 051***	
CONTACTS TYPE CONTACTS/TERMINATIONS: 17 Pin, Surface Mount PLATING OPTIONS: 5 50 μ " Au contacts; Sn/Pb alloy terminations ☒ 8 50 μ " Au contacts; Sn plated terminations		CONTACTS TYPE CONTACTS/TERMINATIONS: 21 Socket, straight, solder cup 24 Socket, straight, .500" pigtails (.018 dia) 25 Socket, straight, 1.000" pigtails (.018 dia) 26 Socket, straight, crimped wire PLATING OPTIONS: 1 50 μ " Au contacts (crimp wire) 3 50 μ " Au contacts: 10 μ " Au terminations (solder cup, pigtail) 5 50 μ " Au contacts; Sn/Pb alloy terminations (pigtail) ☒ 7 50 μ " Au contacts; SAC305 terminations (pigtail)	
HARDWARE STYLE OF HARDWARE: 00 None 32 Two fixed jacknut assemblies with mounting bracket 46 Two turning jackscrews, allen head, captivated** with mounting bracket		HARDWARE STYLE OF HARDWARE: 00 None 22 Two fixed jacknut assemblies 41 Two turning jackscrews, allen head, retaining ring 42 Two long turning jackscrews, allen head, retaining ring 43 Two turning jackscrews, slot head, retaining ring 44 Two long turning jackscrews, slot head, retaining ring 45 Two turning jackscrews, allen head, captivated**	
POLARIZATION / WIRING: 0R Reverse Body Polarization 0S Standard Body Polarization		POLARIZATION / WIRING 00 None XX For wiring codes, see page MA-3 & MA-4	
OPTIONS 900 Interfacial sealing gasket		OPTIONS 900 Interfacial sealing gasket	

** = Captive hardware is factory installed and non-removable.

*** = 51 position connectors are available in metal only (non Mil-Spec interface).

☒ = Option not RoHS compliant