

Coaxial Panel Connector 22_BNO-0-0-1/133_N

Description

Straight bulkhead receptacle jack

Interface standards
IEC 60169-22



Technical Data

Electrical Data

Impedance	not defined Ω
Interface frequency max.	0.2 GHz

Mechanical Data

Number of matings	500
Weight	0.0063 kg

Environmental Data

Operating temperature	-50 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	ETFE (Ethylene tetrafluoroethylene)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	

Related Documents

Outline drawing	DOU-00011411
Catalogue drawing	DCA-00011413
Mounting hole	DOU-00008762

Ordering Information

Single package	22_BNO-0-0-2/133_NE
----------------	---------------------