



Datasheet for part number DCMMC-37P-J-K87

| | |
|---|--|
| Our Catalog Part Number: DCMMC-37P-J-K87 | |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*M | |

| Product Datasheet | |
|---------------------------------|--|
| General | D*M High reliable D-Sub Connectors |
| Wire Gauge Range AWG | AWG 20-28 |
| Mating Cycles | 500 |
| Contact Arrangement | 37 contacts size 20 |
| Dielectric Withstanding Voltage | 1000 VAC at sea level |
| Current Rating | 7.5 A max |
| Contact Resistance | 7.5 milli Ohm max |
| Operating Temperature | -55°/+150° |
| Salt Spray Test | 48 hours {96 Hrs for Stainless Steel} |
| Shell Material | steel |
| Shell Finish | pure tin over nickel |
| Insulator Material | Thermoplastic, type PCT UL 94V-0 |
| Insulator Color | black |
| Gender | Pin |
| Contact Type | Right angled PCB |
| Contact Material | copper alloy |
| Contact Finish | gold over nickel (Performance Class 2) |
| Hardware | 90° Metal Bracket, 4-40 Fastener & Boardlock |
| Disclaimer | Our facility is not currently certified by the DLA and this product is not covered by the QPL/QML. |