

R 15-SCHRAUBKAPPE



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 5401
Specification	R 15-SCHRAUBKAPPE
HARTING eCatalogue	https://b2b.harting.com/09150005401

Identification

Category	Hoods/Housings
Series	R 15
Type of hood/housing	Cover
Description of hood/housing	With fixing cord Thermoplastic

Version

Locking type	Screw locking
--------------	---------------

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Material properties

Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Commercial data

Packaging size	10
Net weight	9.56 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140021792
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors