

Han 48HPR cover angled housing 4XM40



Image is for illustration purposes only. Please refer to product description.

Identification

| | |
|-----------------------------|--------------------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han® HPR |
| Type of hood/housing | Mounting cover |
| Description of hood/housing | Distance bolt M5 for male inserts |

Version

| | |
|----------------------|---|
| Size | 48 B |
| Cable entry | 4x M40 |
| Locking type | Screw locking |
| Field of application | Hoods/housings for harsh outdoor environments |
| Pack contents | 4 distance pieces 4x M6 screw 4 washers |

Technical characteristics

| | |
|--|--|
| Tightening torque (screw locking) | 4 Nm |
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65 IP68 IP69 / IPX9K acc. to ISO 20653 |

Material properties

| | |
|--------------------------------------|---|
| Material (hood/housing) | Aluminium die-cast Corrosion resistant |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (seal) | NBR |
| Material (locking) | Stainless steel |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Nickel Naphthalene |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 500 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140130388 |
| ETIM | EC002314 |
| eCl@ss | 27440208 Cap for industrial connectors |