



Pushing Performance  
Since 1945

# Han-Modular Guard, black



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 9993
Specification	Han-Modular Guard, black
HARTING eCatalogue	<a href="https://b2b.harting.com/09140009993">https://b2b.harting.com/09140009993</a>

## Identification

Category	Accessories
Series	Han-Modular®
Type of accessory	Guide element
Description of the accessory	Han-Modular® Guard for Han-Modular® hinged frames

## Technical characteristics

Limiting temperature	-40 ... +125 °C
----------------------	-----------------

## Material properties

Material (accessories)	Polycarbonate (PC)
Colour (accessories)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate

## Commercial data

Packaging size	10
----------------	----



**Pushing Performance**  
Since 1945

Commercial data

Net weight	1.2 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140194779
ETIM	EC002939
eCl@ss	27440392 Connector (accessories)