SUMICON 1600 SERIES RECTANGULAR CONNECTORS

The SUMICON 1600 series are multi-contact connectors designed by Hirose. 8, 12, 16, 20, 24, 28, 34, 45 and 60-contact models available (same as the 1300 series). The connector units are available in three types: soldering, wrapping, and crimping. Accessories

are C case, CA case, CBA case, ST stopper, STA stopper, and STB stopper, By combining the many options noted above, the SUMICON 1600 series connectors meet a wide variety applications.

Standard Type

General

In the SUMICON 1600 series, the connector unit is completely separated from the accessories such as the cases and stoppers to diversify the specificaions and

facilitate wiring connection. The SUMICON 1600 series are specified in the NTT specifications No.1931.

Electrical Characteristics

Item	Standard	
Contact Resistance	7mΩ max. at DC 1A	
Insulation Resistance	1000M Ω min. at DC 500V	
Withstand Voltage	AC 1000V for 1 minute	
Current Rating	3A	
Voltage Rating	300V AC	


Material and Finish

Part	Material	Finish	
Insulator	Glass filled diallylphthalate resin	Blue	
Male Terminal	Brass	Type A: Silver-plated Type G: Gold-plated	
Female Terminal	Phosphor bronze		
Plug Case ABS resin(black)		NTT spec: ABS resin, 2.5PB 6.0/2.0 (color)	
Stopper Bracket	Steel	Nickel plating	

Wire Wrapping Specifications

Applicable wire	AWG	26	28	30
	Applicable wire (mm)	0.41	0.32	0.26
	Max. coating O.D. (mm)	0.95	0.75	0.6
Wrapping method		Ordinary wrapping	Coating one wrap	Coating one wrap
Effective number of wrappings		about 8	about 8	about 9
Number of wrappings per terminal		2 wrap		


Ordering Information



- (1) Shape of terminal opening P: Male terminal
- S: Female terminal Terminal connection method
 - No sign: Soldering W: Wrapping C: Crimp
- (3) Series No.
 - 16: 1600 series
- (4) Number of contacts 34: 34 contacts
- (5) Serial sign for connctor units Provided with a sequence of upper-case alphabetic charac-
 - No sign or sign other than W: Soldering Sequence: No sign, B, C, D, E ...
- (6) Plating
 - A: Silver-plated
- G: Gold-plated (7) Signs for accessories

- C: Plug case
- ST: Stopper bracket with horizontal cable inlet opening
- J: Jack Case
- H: Handle
- DB: Deep bracket
- Serial signs for accessories
 - Each accessory (C, ST, J, H, DB) is provided with sequence of upper-case. alphabetic characters.
- Sequence: No sign, A, B, C... Accessories, C, ST, or J followed by *no sign* : Side lock
- Accessories, C and ST followed By A: Top touch lock type Note: The space for no sign is filled sequentially.
- Special specification, () is filled with a serial number, except for the case and bracket, for which the following ap
 - ply. (51): Bracket only
 - (50): Case only

Side Touch Lock Type Plug Shell



Side Touch Lock Type Receptacle Bracket

