

D-USB Connectors

1 2 3 4 5 6 7 8 9 10

Specification

> Standard > High Density
(SDB) D-SUB (HDB) High Density D-SUB

Number of Contacts

09,15,,25,26...78 Contacts
Ex. 09 Pin = (09)

Connector Body (Style)

> For Receptacle > For Overmolded with Cable
(P) Front Fastened (A) With Strain Relief
> For Field installable
(B) Without Strain Relief

Connector (Housing) Gender

(M) Male Connector (F) Female Connector

Contact Gender

(M) Male (Plug) (F) Female (Jack)

Assemble Style

> For Receptacle > For Overmolded with Cable
(S) Solder Type (M) Overmolded with Cable
(P) PCB Type (90° / 180°) > For Field Installable
(A) Field Installable (Solder)
(C) Field Installable (Crimped)

Mating Style

(S) Screw Thread (Q) Automated Latch

Backshell

> For Receptacle > For Overmolded with Cable
(With Board Lock) (Without Board Lock)
(A) Straight (L) Straight
(B) Right Angle > For Field Installable
(Without Board Lock) (Without Board Lock)
(L) Straight (L) Straight
(R) Right Angle

Waterproof Rating

(7) IP 67
(8) IP 68

More Information

> For Receptacle > For Overmolded with Cable
(001), (002)..... (□)+(■) : Cable Type + Cable Length
Without Cable : Different EX. (A01) = UL2464 Cable + 1M
Versions (□) : Cable Type (■) : Cable Length
(A) UL2464 Cable From 1M to 99M
EX. (01) = 1M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[HDB-26AMMM-SL7A01](#) [HDB-78AMMM-SL7A05](#) [SDB-15PFFP-SR8001](#) [HDB-62AFFM-SL7A10](#) [HDB-62AMMM-SL7A10](#) [HDB-78AFFM-SL7A05](#) [HDB-78AFFM-SL7A10](#) [HDB-78AMMM-SL7A10](#) [SDB-15PFFP-SA8001](#) [SDB-15PMMP-SR8001](#) [SDB-25AFFM-SL7A01](#) [SDB-25AFFM-SL7A02](#) [SDB-25AFFM-SL7A10](#) [SDB-25AMMM-SL7A02](#) [SDB-25AMMM-SL7A10](#) [SDB-25PMMP-SA8001](#) [SDB-37AFFM-SL7A01](#) [SDB-37AFFM-SL7A02](#) [SDB-37AFFM-SL7A05](#) [SDB-37AFFM-SL7A10](#) [SDB-37AMMM-SL7A02](#) [SDB-37AMMM-SL7A10](#) [SDB-50AFFM-SL7A01](#) [SDB-50AFFM-SL7A05](#) [SDB-50AFFM-SL7A10](#) [SDB-50AMMM-SL7A01](#) [SDB-50AMMM-SL7A02](#) [SDB-50AMMM-SL7A05](#) [SDB-50AMMM-SL7A10](#) [HDB-44PMMP-SB8001](#) [SDB-25PMMP-SB8001](#)