

# Han 10A-Cover-Plastic 2 Pins, f. BP



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 010 5410
Specification	Han 10A-Cover-Plastic 2 Pins, f. BP
HARTING eCatalogue	<a href="https://b2b.harting.com/09200105410">https://b2b.harting.com/09200105410</a>

## Identification

Category	Accessories
Series of hoods/housings	Han A <sup>®</sup>
Type of accessory	Protection cover
Description of the accessory	for bearing pedestal

## Version

Size	10 A
Locking type	Single locking lever

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

## Material properties

Material (accessories)	Thermoplastic
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes



Pushing Performance  
Since 1945

Material properties

California Proposition 65 substances	Nickel
	Naphthalene

Commercial data

Packaging size	1
Net weight	18.3 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140039537
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors