






Solderpot position

A-A



2:1

RoHS compliant
by exemption

Crimping tools:

Crimping of outer conductor:


Hand tool: 1731121732

Die: 1731121735 cavity A

Pneumatic crimp tool: HX23
(replacement for PH4001)

Extraction tool: 1731121747

Cable trimming dimensions



Customer cable

1731120167	FMX007S102	102
Material Number	FCT Part Number	Material + Finish See extra sheet

UNLESS OTHERWISE SPECIFIED DIMENSIONS FOR REFERENCE ONLY					REPLACEMENT FOR DOCUMENT NUMBER: FMX007S								
FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				molex FCT 50 OHM COAXIAL CONTACT FOR D-SUB								
	CURRENT REV DESC:												
	EC NO: 710219												
	DRWN: VLOKESHA												
DIVISIONAL SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		2021/04/23		PRODUCT CUSTOMER DRAWING								
	ANGULAR TOL ± °		2022/06/22										
	4 PLACES ±		2022/06/22										
	3 PLACES ±		2022/06/22										
	2 PLACES ±		2022/06/22										
	1 PLACE ±		2022/06/22										
0 PLACES ±		2022/06/22		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		FIRST ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				A4-SIZE		173112		SEE TABLE		GENERAL MARKET		1 OF 1	

DOCUMENT STATUS	P1	RELEASE DATE	2022/06/22	10:22:27
-----------------	----	--------------	------------	----------