







4 CIRCUIT SHOWN

REF. -50 OPT. SCREW  
(WHERE APPLICABLE)

## NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: NOT REQUIRED
4. PACKAGING: NOT REQUIRED
5. MATES WITH: N/A
6. "XX" REFERS TO THE QUANTITY OF CIRCUITS.

| 6    | XX   | SCREW&WASHER, #6-32X.250 PAN, PH-SL, -50 | STEEL       | ZN, CLEAR CHROMATE |
|------|------|------------------------------------------|-------------|--------------------|
| 5    | XX   | SCREW, #6-32X.250 BHD, PHIL-SLOT, -49    | BRASS       | NICKEL PLATE       |
| 4    | XX   | SCREW, #6-32X.250 BHD, PHIL-SLOT (STD)   | STEEL       | ZN, CLEAR CHROMATE |
| 3    | XX   | TERMINAL, FAST TAB, STYLE 9, SN/B        | BRASS       | TIN PLATE          |
| 2    | 2    | PLATE, MOUNTING, NI                      | BRASS       | NICKEL PLATE       |
| 1    | 1    | INSULATOR, 9.53MM, SR BTS, INSUL. BASE   | PBT, 30% GF | BLACK              |
| ITEM | QTY. | DESCRIPTION                              | MATERIAL    | FINISH             |

|            |                     |              |            |
|------------|---------------------|--------------|------------|
| RELEASED   | EC NO: ETC2006-0262 | 2006/02/20   | 2006/02/21 |
| DRWN:CYORK | CHKD:RDEROSS        | APPR:RDEROSS | 2006/02/16 |
| REV        | A                   | DESCRIPTION  |            |

|                 |
|-----------------|
| QUALITY SYMBOLS |
| ▽=0             |
| ▽=0             |

| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                   |         |        |
|------------------------------------------------------------|---------|--------|
|                                                            | mm      | INCH   |
| 4 PLACES                                                   | ± ---   | ±.0002 |
| 3 PLACES                                                   | ± 0.005 | ±.005  |
| 2 PLACES                                                   | ± 0.13  | ±.01   |
| 1 PLACE                                                    | ± 0.25  | ± ---  |
| ANGULAR ± 1 °                                              |         |        |
| DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS |         |        |

| DIMENSION STYLE | MM/IN      |
|-----------------|------------|
| DRAWN BY        | DATE       |
| C. YORK         | 2006/02/16 |
| CHECKED BY      | DATE       |
| RDEROSS         | 2006/02/16 |
| APPROVED BY     | DATE       |
| RDEROSS         | 2006/02/16 |
| MATERIAL NO.    |            |
| SEE SHEET 2     |            |
| SIZE            | B          |

| SCALE                                                                                                                         | DESIGN UNITS | THIRD ANGLE PROJECTION |
|-------------------------------------------------------------------------------------------------------------------------------|--------------|------------------------|
| 2:1                                                                                                                           | INCH         |                        |
| 9.53 [.375] SR BTS ASY, INSUL. FT, W/MTG                                                                                      |              |                        |
| MOLEX INCORPORATED                                                                                                            |              |                        |
| DOCUMENT NO.                                                                                                                  |              | SHEET NO.              |
| SD-38721-002                                                                                                                  |              | 1 OF 2                 |
| THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |              |                        |



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38721-7316](#) [38721-7318](#) [38721-7303](#) [38721-6714](#) [38721-6716](#) [38721-7002](#) [38721-7003](#) [38721-7004](#) [38721-7005](#) [38721-7006](#) [38721-7008](#) [38721-7009](#) [38721-7012](#) [38721-7022](#) [38721-7305](#) [38721-7307](#) [38721-7309](#) [38721-7310](#) [38721-7311](#) [38721-7312](#) [38721-7313](#) [38721-7314](#) [38721-7315](#) [38721-7322](#)