



Pushing Performance  
Since 1945

# UIC558-HBM/CM-13PIN



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 001 0301
Specification	UIC558-HBM/CM-13PIN
HARTING eCatalogue	<a href="https://b2b.harting.com/09580010301">https://b2b.harting.com/09580010301</a>

## Identification

Category	Hoods/Housings
Series	HARTING UIC
Identification	UIC 558
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With metal cover

## Version

Number of contacts	13
Field of application	Hoods/housings for harsh outdoor environments

## Technical characteristics

Limiting temperature	-50 ... +125 °C
Degree of protection acc. to IEC 60529	IP69 / IPX9K acc. to ISO 20653 mated condition

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7035 (light grey)
Material (seal)	Silicone
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant



Pushing Performance  
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UIC 50558
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

Commercial data

Packaging size	1
Net weight	581.06 g
Country of origin	India
European customs tariff number	85389099
GTIN	5713140183919
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors