

RoHS

REV	ECN NO.	DESRPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24

SPECIFICATIONS

- Current rating: 3A
- Temperature range: -40°C ~ +105°C
- Insulation resistance: 1000MΩ Min.
- Withstanding voltage: 600V AC/ minute.
- Contact resistance: 20mΩ Max.





Material:

Insulator Material:PA6T(UL 94V-0)
Contact Material:Brass
Contact plating :Gold float or Su over Ni
Mate with XFCN PM254 Single row series

Ordering Code:

PZ254VS-11-XX-A01
1 2 3

- 序列号
- Pin位数: 02-40P
- 包装: 01=袋装
02=加盖卷装



PCB LAYOUT

X.±0.50	X.°±	PART NO: PZ254VS-11-XX-A01		XFCN 兴飞连接器				
.X±0.25	.X°±							
.XX±0.15	.XX°±	TITLE: 2.54mm Pin Header Connectors		0769-82001899				
.XXX±0.10	.XXX°±			www.xfconn.com				
UNITS:	mm	APPD Chen ZhiQiang		DWG NO: /				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN				CHKD Liu Wei		VIEW		
				DRAW Chen HongJiang		SCALE	SHEET	REV
				DATE 2024.10.09		NONE	1/1	A1