

## Han TC100 female contact 35 mm<sup>2</sup> Han K6/6



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 6629
Specification	Han TC100 female contact 35 mm <sup>2</sup> Han K6/6
HARTING eCatalogue	<a href="https://b2b.harting.com/09110006629">https://b2b.harting.com/09110006629</a>

### Identification

Category	Contacts
Series	TC 100
Type of contact	Crimp contact

### Version

Gender	Female
Manufacturing process	Turned contacts
Details	Only for use in the Han <sup>®</sup> K 6/6

### Technical characteristics

Conductor cross-section	35 mm <sup>2</sup>
Rated current	≤100 A
Contact resistance	≤0.3 mΩ
Stripping length	16 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	10
Net weight	12.35 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188228
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors