




(0.635 mm) .025" PITCH • QMSS/QFSS SERIES

NRZ

14
G b p s



QMSS
Board Mates:
QFSS

QFSS
Board Mates:
QFSS


QMSS/QFSS
Standoffs:
SO

SPECIFICATIONS

Insulator Material:
Liquid Crystal Polymer
Terminal, Ground Plane & Shield Material:
Phosphor Bronze
Plating:
Au over 50 μ " (1.27 μ m) Ni
(Tin on Ground Plane Tail)
Operating Temp Range:
-55 °C to +125 °C
Voltage Rating:
300 VAC

PROCESSING

Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0.10 mm) .004" max
(026-078)
Board Stacking:
For applications requiring more than two connectors contact ipg@samtec.com



Note:
Some lengths, styles and options are non-standard, non-returnable.

QMSS	PINS PER ROW NO. OF PAIRS	06.75	PLATING OPTION	TYPE	A	OTHER OPTION
------	------------------------------	-------	-------------------	------	---	-----------------

-026, -052, -078
(52 total pins per bank / 40 signals
+ 12 grounds to shield = -D)




-016, -032, -048
(16 pairs per bank = -D-DP)

-L
= 10 μ " (0.25 μ m)
Gold on contact,
Matte Tin on tail


-D
= Single-
Ended
-D-DP
= Differential
Pair

-K
= (5.50 mm)
.217" DIA
Polyimide
film Pick &
Place Pad
(N/A with
-PC4)

-PC4
= 4 Power
Pins/End
(N/A with -A)



-PC4 OPTION



PACKAGING OPTION

Tape & Reel
Options
(-TR & -FR)
available. Visit
series web
page and view
engineering prints
for complete
specifications.

View complete specifications at: samtec.com?QMSS

QFSS	PINS PER ROW NO. OF PAIRS	04.25	PLATING OPTION	TYPE	A	OTHER OPTION
------	------------------------------	-------	-------------------	------	---	-----------------




-026, -052, -078
(52 total pins per bank / 40 signals
+ 12 grounds to shield = -D)

-016, -032, -048
(16 pairs per bank = -D-DP)



-L
= 10 μ " (0.25 μ m)
Gold on contact,
Matte Tin on tail

-D
= Single-
Ended
-D-DP
= Differential
Pair

-PC4
= 4 Power
Pins/End
(N/A with -A)



-PC4 OPTION



PACKAGING OPTION

Tape & Reel
Options
(-TR & -FR)
available. Visit
series web
page and view
engineering prints
for complete
specifications.

View complete specifications at: samtec.com?QFSS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[QFSS-052-04.25-L-D-A](#) [QFSS-016-04.25-L-D-DP-PC4](#) [QFSS-026-04.25-L-D-A](#) [QFSS-026-04.25-L-D-PC4](#) [QFSS-048-04.25-L-D-DP-A](#) [QFSS-016-04.25-L-D-DP-A](#) [QFSS-032-04.25-L-D-DP-PC4](#) [QFSS-052-04.25-L-D-PC4](#) [QFSS-026-04.25-H-D-A-GP](#) [QFSS-026-04.25-H-D-A](#) [QFSS-052-04.25-H-D-PC4](#) [QFSS-052-01-L-D-A-PC8](#) [QFSS-052-01-L-D-A](#) [QFSS-016-04.25-H-D-DP-PC4](#) [QFSS-016-04.25-H-D-DP-PC8](#) [QFSS-026-04.25-L-D-GP](#) [QFSS-048-04.25-H-D-DP-A](#) [QFSS-052-04.25-L-D-A-P-TR](#) [QFSS-052-04.25-L-D-A-TR](#) [QFSS-104-04.25-H-D-A](#) [QFSS-104-04.25-L-D-A](#) [QFSS-016-04.25-L-D-DP-PC8](#) [QFSS-048-04.25-L-D-DP-A-P](#) [QFSS-052-04.25-H-D-A-P-TR](#) [QFSS-016-04.25-H-D-DP](#) [QFSS-016-04.25-L-D-DP-P](#) [QFSS-026-04.25-H-D-PC8](#) [QFSS-032-04.25-L-D-DP](#) [QFSS-032-04.25-L-D-DP-A-GP](#) [QFSS-052-04.25-L-D-PC4-P-TR](#) [QFSS-064-04.25-L-D-DP-A](#) [QFSS-078-04.25-L-D-A-TR](#) [QFSS-016-04.25-L-D-DP-A-GP](#) [QFSS-026-04.25-L-D-P-TR](#) [QFSS-032-04.25-H-D-DP-PC8](#) [QFSS-032-04.25-L-D-DP-A](#) [QFSS-048-04.25-L-D-DP-A-GP](#) [QFSS-026-04.25-H-D](#) [QFSS-032-04.25-H-D-DP](#) [QFSS-032-04.25-H-D-DP-A-GP](#) [QFSS-032-04.25-H-D-DP-PC4](#) [QFSS-048-04.25-L-D-DP-PC4](#) [QFSS-052-04.25-H-D-A-P](#) [QFSS-064-04.25-L-D-DP](#) [QFSS-078-04.25-L-D-A-P-TR](#) [QFSS-016-04.25-H-D-DP-A](#) [QFSS-026-04.25-H-D-PT4](#) [QFSS-026-04.25-L-D-PC8](#) [QFSS-048-04.25-L-D-DP-A-P-TR](#) [QFSS-052-04.25-H-D-PC4-P-TR](#) [QFSS-078-04.25-L-D-PC4](#) [QFSS-016-04.25-L-D-DP](#) [QFSS-026-04.25-L-D-A-GP](#) [QFSS-026-04.25-L-D-A-TR](#) [QFSS-048-04.25-H-D-DP-PC4](#) [QFSS-052-04.25-L-D-A-GP](#) [QFSS-026-04.25-H-D-A-BM](#) [QFSS-052-04.25-H-D-A](#) [QFSS-052-04.25-H-D-A-GP](#) [QFSS-078-04.25-H-D-A](#) [QFSS-078-04.25-L-D](#) [QFSS-026-04.25-L-D](#) [QFSS-026-04.25-L-D-PC4-TR](#) [QFSS-026-04.25-L-D-PT4](#) [QFSS-052-04.25-L-D](#) [QFSS-078-04.25-L-D-A-P](#) [QFSS-052-04.25-L-D-P](#) [QFSS-026-04.25-L-D-A-P-TR](#) [QFSS-048-04.25-L-D-DP](#) [QFSS-078-04.25-L-D-PC4-P](#) [QFSS-078-04.25-L-D-PT4](#) [QFSS-026-04.25-H-D-A-P-TR](#) [QFSS-026-04.25-H-D-PC4](#) [QFSS-032-04.25-H-D-DP-A](#) [QFSS-048-04.25-L-D-DP-P](#) [QFSS-078-04.25-H-D-PC4](#) [QFSS-078-04.25-L-D-A](#) [QFSS-104-04.25-L-D-A-GP](#) [QFSS-016-04.25-L-D-DP-PT8](#) [QFSS-064-04.25-L-D-DP-GP](#) [QFSS-032-04.25-L-D-DP-PT4](#) [QFSS-064-04.25-L-D-DP-A-GP](#) [QFSS-016-04.25-L-D-DP-A-P-TR](#) [QFSS-032-04.25-L-D-DP-PT8](#) [QFSS-026-04.25-L-D-PT8](#) [QFSS-078-04.25-H-D-A-GP](#) [QFSS-052-04.25-H-D-A-TR](#) [QFSS-032-04.25-L-D-DP-A-P](#) [QFSS-032-04.25-L-D-DP-A-TR](#) [QFSS-048-04.25-L-D-DP-PT4](#) [QFSS-052-04.25-L-D-PT4](#) [QFSS-016-04.25-L-D-DP-PC4-P](#) [QFSS-078-04.25-L-D-PC8](#) [QFSS-026-04.25-H-D-PC4-TR](#) [QFSS-026-04.25-L-D-P](#) [QFSS-016-04.25-L-D-DP-PT4](#) [QFSS-032-04.25-L-D-DP-A-P-TR](#) [QFSS-026-04.25-L-D-A-BM](#) [QFSS-026-04.25-L-D-PC4-P](#) [QFSS-032-04.25-L-D-DP-A-GP-P](#)