

PS-7,5/2,3MM RD - Test plug



3038749

<https://www.phoenixcontact.com/us/products/3038749>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, number of positions: 1, color: red

Your advantages

- The test plug reliably makes contact in the bridge shaft and in all test sockets with a 2.3 mm or 4 mm diameter
- Individual test adapters can be combined using the modular PS-...2,3MM test plug.
- The test plugs are inserted in the function shaft of the terminal blocks from the CLIPLINE complete system or in the test pick-offs provided
- Housing for test plugs, any combination

Commercial data

Item number	3038749
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
Catalog page	Page 591 (C-1-2019)
GTIN	4017918904159
Weight per piece (including packing)	1.47 g
Weight per piece (excluding packing)	1.25 g
Customs tariff number	85366990
Country of origin	DE

PS-7,5/2,3MM RD - Test plug

3038749

<https://www.phoenixcontact.com/us/products/3038749>



Technical data

Product properties

Product type	Test plug terminal block
Number of positions	1
Pitch	7.5 mm

Data management status

Article revision	01
------------------	----

Connection data

Connection method	Spring-cage connection
-------------------	------------------------

Dimensions

Width	7.5 mm
Height	14 mm
Depth on NS 35/7,5	36 mm
Pitch	7.5 mm

Material specifications

Color	red (RAL 3001)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C ()
Permissible humidity (storage/transport)	30 % ... 70 %

PS-7,5/2,3MM RD - Test plug

3038749

<https://www.phoenixcontact.com/us/products/3038749>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3038749>



EAC

Approval ID: RU C-DE.BL08.B.00511

PS-7,5/2,3MM RD - Test plug



3038749

<https://www.phoenixcontact.com/us/products/3038749>

Classifications

ECLASS

ECLASS-11.0	27440313
ECLASS-12.0	27440313
ECLASS-13.0	27440313

ETIM

ETIM 9.0	EC002255
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

PS-7,5/2,3MM RD - Test plug



3038749

<https://www.phoenixcontact.com/us/products/3038749>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4b22e0f3-6445-4f44-86f9-384d1e91a1d4

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com