MALLORY Mallory Sonalert Products Inc.	Part #	AST0927ME-05Q
Sales Outline Drawing	Revision	C

May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.


NO CIRCUITRY


110 CIRCUIRI			
Oscillation Frequency (Hz)	2731		
Operating Voltage (Vp-p)	4.0 ~ 7.0		
Rated Voltage (Vp-p)	5.0		
Current Consumption Max. (mA)	80 at Rated Voltage		
Sound Pressure Level (dB/min)	85 at 10cm at Rated Voltage		
Coil Resistance (Ω)	32 ± 3		
Operating Temperature (°C)	-20 ~ +70		
Storage Temperature (°C)	-30 ~ +80		
Mounting	SMD		
Housing	LCP plastic resin (Color: Black)		
Weight (Grams)	0.4		
Condition by wave soldering (°C)	250 ± 5 / within 5 sec		
Condition by hand soldering (°C)	350 ± 20 / within 5 sec		
Options	For other options contact factory		

Dimensions: (units: mm)

PS: Vp-p = 1/2duty, square wave

ROHS Compliant





Packaging:

Parts are supplied as Cut Tape.

Units do not come with wash label and are not appropriate for aqueous wash.