

Han 32A-Cover w. cord (Plastic)



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 032 5408
Specification	Han 32A-Cover w. cord (Plastic)
HARTING eCatalogue	https://b2b.harting.com/09200325408

Identification

Category	Accessories
Series of hoods/housings	Han A [®]
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings
	for surface mounted housings
	Thermoplastic
	With fixing cord

Version

Size	32 A
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	32.5 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140191808
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors