

2





1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	WIRE	WIRE STRIP LENGTH	STUD HOLE	OVERALL LENGTH REF	OVERALL HEIGHT REF	B ±.08	D ±.01	E ±.01	G ±.1	C ±.1	T ±.03	W ±.03
A6-14RH-C	6	9/16"	1/4	1.33	0.79	0.50	0.31	0.23	0.32	0.76	0.07	0.54
A2-14RH-C	2	3/4"	1/4	1.71	1.20	0.74	0.42	0.31	0.36	0.74	0.10	0.60
A2-56RH-C	2	3/4"	5/16	1.78	1.20	0.74	0.42	0.31	0.36	0.80	0.10	0.66
A2-38RH-C	2	3/4"	3/8	1.80	1.20	0.74	0.42	0.31	0.36	0.83	0.10	0.66
A1/0-38RH-C	1/0	13/16"	3/8	1.93	1.30	0.80	0.52	0.39	0.37	0.84	0.12	0.76
A2/0-56RH-C	2/0	15/16"	5/16	1.89	1.53	0.88	0.58	0.45	0.35	0.80	0.13	0.85
A2/0-38RH-C	2/0	15/16"	3/8	1.99	1.42	0.88	0.58	0.45	0.45	0.90	0.13	0.85
A4/0-38RH-C	4/0	15/16"	3/8	2.39	1.62	0.91	0.69	0.56	0.52	1.14	0.12	1.02
A4/0-12RH-C	4/0	15/16"	1/2	2.39	1.62	0.91	0.69	0.56	0.52	1.14	0.12	1.02

- NOTES:
- MATERIAL: HIGH CONDUCTIVITY SEAMLESS COPPER TUBE
 - PLATING: ELECTRO-TIN
 - WIRE TYPE: STRANDED COPPER; CLASS K



SECTION A - A

01B	6-20-23	JHNU	JHNU	MRWA	C. ADDED PACKAGING CODE TO PART NUMBERS	131601
01A	4-27-23	JHNU	JHNU	MRWA	B. ADDED cULus LOGO A. CONVERTED DRAWING TO NX	130501
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

PART NUMBER		SEE TABLE			
TITLE		BATTERY CABLE LUG BENT 45			
ITEM REVISION NAME		CUSTOMER DRAWING			
DATASET FILE NAME		00374EBA-DC/01B			
MATERIAL		SEE NOTES			
DRAWN BY		DATE		CHK	SCALE
RUMO		10-8-18		RGB	NONE
DRAWING NUMBER		00374EBA-DC			
SHEET 1 OF 1		SIZE			
		B			

2



1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[A6-14RH-C](#) [A4/0-38RH-C](#) [A2/0-38RH-C](#) [A2-14RH-C](#) [A2-56RH-C](#) [A1/0-38RH-C](#) [A4/0-12RH-C](#) [A2-38RH-C](#)