

UIC558-FC-CRT-0.75-1.0 mm²/18 AWG-AG



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 000 6205
Specification	UIC558-FC-CRT-0.75-1.0 mm ² /18 AWG-AG
HARTING eCatalogue	https://b2b.harting.com/09580006205

Identification

Category	Contacts
Series	HARTING UIC
Identification	UIC 558
Type of contact	Crimp contact

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.75 ... 1 mm ²
Conductor cross-section [AWG]	AWG 18
Rated current	≤10 A
Contact resistance	≤4 mΩ
Stripping length	7.5 mm
Mating cycles	≥10,000

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated

Specifications and approvals

Specifications	UIC 50558 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	---

Commercial data

Packaging size	50
Net weight	1.7 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140188662
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors