

# AP RSC - Cover profile



3058017

<https://www.phoenixcontact.com/us/products/3058017>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover profile, for covering terminal strips, directly snapped onto RBO... and RSC... terminal blocks. Length supplied: 1 m

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3058017             |
| Packing unit                         | 10 m                |
| Minimum order quantity               | 10 m                |
| Sales key                            | BE06                |
| Product key                          | BE61ZX              |
| Catalog page                         | Page 387 (C-1-2019) |
| GTIN                                 | 4046356520317       |
| Weight per piece (including packing) | 190 g               |
| Weight per piece (excluding packing) | 190 g               |
| Customs tariff number                | 39162000            |
| Country of origin                    | DE                  |

# AP RSC - Cover profile

3058017

<https://www.phoenixcontact.com/us/products/3058017>



## Technical data

### Product properties

|                        |               |
|------------------------|---------------|
| Product type           | Cover profile |
| Data management status |               |
| Article revision       | 00            |

### Dimensions

|        |         |
|--------|---------|
| Width  | 53.3 mm |
| Height | 1000 mm |
| Depth  | 18.1 mm |
| Length | 1 m     |

### Material specifications

|          |             |
|----------|-------------|
| Color    | transparent |
| Material | PVC         |

### Environmental and real-life conditions

#### Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

# AP RSC - Cover profile



3058017

<https://www.phoenixcontact.com/us/products/3058017>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27141190 |
| ECLASS-12.0 | 27141190 |
| ECLASS-13.0 | 27141190 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002848 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# AP RSC - Cover profile



3058017  
<https://www.phoenixcontact.com/us/products/3058017>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)