

Han 32B-C-f. HSM / HBM w. cord (Plastic)



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 032 5406
Specification	Han 32B-C-f. HSM / HBM w. cord (Plastic)
HARTING eCatalogue	https://b2b.harting.com/09300325406

Identification

Category	Accessories
Series of hoods/housings	Han® B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings
	for surface mounted housings
	Thermoplastic
	With fixing cord

Version

Size	32 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	39 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140162051
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors