

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



CB-XXAFFM-RL7A XX

Middle Size Current Rating 10A

XX:No. Of Pin(Pin 數)

A:Cable With S/R(線端帶網尾)

F:Female Connector(母座)

F:Female Pin(母Pin)

M:Molding Type(射出成型)

XX:01~99Meter

01:01Meter

02:02Meter

...



99:99Meter

A:UL 2464 Cable

7:IP67(防水等級 67)

L:Straight(180°)

R:Snap In With Latch(彈臂卡合式)




Pin Out

4 --
3 Red 紅
2 --
1 Black 黑


4 Green 綠
3 White 白
2 --
1 Black 黑

4 Orange 橙
3 Red 紅
2 Brown 棕
1 Black 黑


Pin
Assignments
Front View



2Pin




3Pin



4Pin

UNIT:mm



TOLERANCE
±0.5

TITLE

MIDDLE
CABLE RBL F CONN F PIN

SCALE 3:4

SIZE A4

SHEET 2 OF 2

REV. C

WC-REV. A.2

QC: Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO

CB-XXAFFM-RL7AXX

CUSTOMER

ALTW

DRAWN BY

Mafei

CHECKED BY

Joyy

APPROVED BY

Jerry

DATE

2016/08/06

DATE

2016/08/06

DATE

2016/08/06