

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202340011

Status:

Active

Overview:

Brad M23 Signal and Power Connectors

Description:

Brad M23 Power Connector, Front Panel-Mount Receptacle, 90° Male, Flange Mount
4xØ 2.70mm, Rotatable Flange 25x25mm, Crimp Contacts, 8 (4+3+PE) Poles

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Field Attachable / Accessories
Series	120234
Application	Power
Comments	Crimp Range 0.25-1.0mm² / 0.75-2.50mm², Crimp Range 0.25-1.0mm² / 0.75-2.50mm²
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M23 Signal and Power Connectors
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906301675
Physical	
Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold over Nickel
Orientation	90° Angle
Poles	8 (4+3+PE)
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	28.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	KRP8G07-1112
Reference - Drawing Numbers	
Sales Drawing	SD-120234-003



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120234 Series