



Part Number : 936014537
Product Description : GWconnect STD - Standard, Single Lever Coupler, Polyamide, with 1 Lever, Top Entry, with Cable Gland, Size «32x13», Pg21 Thread, Black
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Number : 7908.6668.1



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Heavy-Duty Connectors
Series	93601
Description	GWconnect STD - Standard, Single Lever Coupler, Polyamide, with 1 Lever, Top Entry, with Cable Gland, Size «32x13», Pg21 Thread, Black
Component Type	Single Lever Coupler
IP Rating	IP66, IP67
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191843018

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V
-------------------	------

Physical

Cable Diameter	11.00-18.00mm
Component Size	«32X13»
Entry Location	Top
Flammability	UL 94V-0
Gland Color	Black RAL 9005
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide
Material - Hood	Polyamide
Material - Lever	Polyamide
Net Weight	42.000/g
Number of Levers	1
Packaging Type	Bag

Thread Size	Pg21
Thread Type	(Pg)

Use with Part(s)

Description	Part Number
Use With	Size «32x13» S-QD Inserts