





NOTES:

1. Material/材质: See Table-1/见表-1;
2. Finish/表面处理: Tin-Plated/镀锡;
3. Wire Size Range/线规: See Table-1/见表-1;
4. Contact surface should not have burrs, Other areas burr 0.10mm Max.
端子接触面不能有毛刺, 其他区域毛刺不能超过0.10mm;
5. RoHS Compliance/产品符合RoHS;
6. Order Information/编码原则: 932-080-101X
See Table-1/见表-1

Table-1

P/N	E	F	G	H	MARK	适用铜线径	适用线被外径
932-080-1011	2.1	1.4	2.26	1.8	X	0.13mm ²	φ0.85 mm
932-080-1012	2.1	2.1	2.6	2.6	S	0.35mm ²	φ1.10 mm
932-080-1013	2.5	2.6	2.65	2.7	M	0.50mm ²	φ1.25 mm

X. ± 0.35	X.° ± 5°		Guangdong JiDe Precision Electronics Co., Ltd 广东济德精密电子有限公司			
.X ± 0.25	.X° ± 3°					
.XX ± 0.15	.XX° ± /					
.XXX ± 0.05	.XXX° ± /					
UNITS:	mm	TITLE: 0.80mm MALE TERMINAL		PART NO. 932-080-101X		
The information in this document is property of JIDCON company and should not be copied or reproduced in any other way, without written permission.		APPD:		DWG NO. C-932-080-101X		
		CHKD:				
		DRAW:			SCALE 4:1	SHEET 1/1