







THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1660010	2016/05/27	Vicky	Update Nut Dime




QC White Printing



- Note:
- * $\varnothing$ Important Dimension To Check
 - * Waterproof Rate: IP68
 - * Working Voltage Rating: AC 300V
 - * Working Current: 5A
 - * Housing: Nylon+GF, Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Liquid Glue: Black
 - * Nut: Nylon+GF, Black
 - * Gasket: Silicone, Gray
 - * Panel Thickness Max: 3.6mm



Pin Assignments
Front View



Recommended Panel
Cut-Out

UNIT:mm		TITLE		Amphenol LTW		ITEM NO	DD-14RMMS-QC8001	DRAWN BY	Vicky	DATE	2016-05-27
TOLERANCE		X-Lok D Size		安費諾亮泰企業股份有限公司		DWG NO	DD-14RMMS-QC8001	CHECKED BY	Rita	DATE	2016-05-27
.X ±0.25		Receptacle Rear 14P M Conn M Pin				CUSTOMER	ALTW	APPROVED BY	Lisa	DATE	2016-05-27
.XX ±0.1		SCALE	3:2	SIZE	A4						
.XXX ±0.05		REV.	B	WC-REV.	A.2						
ANGLES ±1°											