

Han-Yellock 30 HSM 2xM25



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Surface mounted housing

Version

Locking type	Screw locking
Size	Han-Yellock® 30
Version	Side entry
Cable entry	2x M25
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7021 (black grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0

Material properties

RoHS compliant

ELV status compliant

China RoHS e

REACH Annex XVII substances No

REACH ANNEX XIV substances No

REACH SVHC substances No

Specifications and approvals

Specifications EN 60664-1
IEC 61984

Approvals DNV GL

CE Yes

Commercial data

Packaging size 1

Net weight 402 g

Country of origin China

European customs tariff number 85389099

eCI@ss 27440202 Shell for industrial connectors